




2	Type
RG	With plastic knurled knob GN 7336
KG	With plastic wing knob
HG	With plastic lever
SG	With star knob
KGN	With wing knob
HGN	With lever



h ₁	Latch arm distance A														h ₂	s max.
30	18	22	26	30	32	34	36	38	40	42	46	50	52	62	40	20
50	38	42	46	50	52	54	56	58	60	62	66	70	72	82	60	40

Specification

Lock housing

Stainless steel

• AISI 316 at h₁ = 30

• AISI 303 at h₁ = 50

• Plain finish

Bolt

Stainless steel AISI 304

Operating element

• Stainless steel AISI 304 for type SG

Sheet metal drawn and hub welded

• Stainless steel AISI CF-8 for type KGN / HG

• Plastic, Polyamide (PA) for type RG / KG / HG

Black, matte finish

Other parts

Stainless steel AISI 303

Protection class IP 65

RoHS

Accessory

GN 120.4 Electromechanical Locking Systems QVX

GN 123 Sheet Metal Punches QVX

GN 120.2 Protective Guide Plates ganternorm.com

GN 120.3 Internal Cabinet Handles ganternorm.com

Latches GN 515 are identical to standard latches GN 115 except for the extended housing. They are operated with a rotation limited to 90°, which moves the latch arm into the locked position behind the frame. The bevels of the latch arm ease the closing of the door.

Thanks to the stainless steel material, the latches are optimally suited for use in corrosive environments.

By installing latch arms with different bend profiles, the latch distance A can be varied from 18 to 82 mm depending on the housing height h₁, while the extended housing is suitable for a door thickness s up to 40 mm.

Latches GN 515 are supplied with loosely enclosed latch arm.

Technical Information	Page
Construction and Assembly Instructions	QVX
Overview of Latch Types	QVX
IP Protection Classes	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order	1	Material
	2	Type
	3	h ₁
	4	Latch arm distance A
	5	Finish
GN 515-NI-KGN-50-62-BL		