



**elesa**

Original design I.680 SOFT



<b>1</b> $d_1 +0,5$	<b>2</b> $d_2$	$d_3$	$l_1$	$l_2$ min.	$l_3$
24	M 8	20,5	65	30	7
24	M 10	20,5	65	40	7
26	M 8	21	80	40	7
26	M 10	21	80	55	7
26	M 12	21	80	55	7
28	M 10	22	90	56	7
28	M 12	22	90	58	10

**Specification**

**Base body**

Plastic, Polypropylen (PP)

**Softline coating**

Thermoplastic elastomer (TPE)

- Chemically bonded with base body
- FDA compliant material
- Operating temperature 0 °C to +80 °C
- Black, matte finish
- Hardness 70 Shore A

RoHS

The Softline coating makes the cylindrical knobs GN 519.6 particularly user-friendly and ergonomic.

The soft, antislip contact area improves the contact both in hot (hand perspiration) and in dry ambient conditions, in the event of oily surfaces and even high or low temperatures.

**see also...**

**GN 519** Cylindrical Knobs (Phenolic Resin) **Page** QVX

**GN 519.1** Cylindrical Knobs (Press-On Type) QVX

**Technical Information**

Product Family Softline QVX

Plastic Characteristics QVX

**How to order**

**GN 519.6-26-M10**

**1**  $d_1$

**2**  $d_2$

