



<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub>	<b>3</b> Length l			d <sub>3</sub>	b	h <sub>1</sub>	h <sub>2</sub>
32	M 6	10	16	20	11	13	14,5	5,5
40	M 8	16	25	-	14	15,5	17	7,5
48	M 8	16	25	-	17	19	19	9
56	M 10	20	30	-	18,5	21	23	11

**Specification**

- Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 130 °C  
- Black, matte finish
- Threaded stud  
Steel  
Zinc plated, blue passivated
- *Plastic Characteristics* → Page 2158
- **RoHS**

**Information**

- see also...
- *Wing Screws GN 531* → Page 615
  - *Wing Screws GN 633* → Page 608
  - *Wing Screws GN 639* → Page 613

How to order

**GN 531.1-56-M10-20**

<b>1</b>	d <sub>1</sub>
<b>2</b>	d <sub>2</sub>
<b>3</b>	Length l

