



2 Bore code

- B** Without keyway
- K** With keyway

4 Type

- A** Without handle
- R** With revolving handle

1 3

d ₁	d ₂ H7 Bore		Type A		Type R		d ₃	d ₄	d ₅	d ₆	d ₇	b	h	l ₁	l ₂	l ₃	r	Ø Handle
80	8	10	-	-	8	10	18	16	25	19	21	20	8	17	29	45	30,5	16
100	8	10	12	10	12	12	22	20	30	25	27	24	9	22	34	60	39	18
125	-	-	-	12	14	14	26	24	35	28	31	28	11	27	39,5	60	49	18
150	14	-	-	14	16	16	26	24	38	30	34	32	10	30	44	65	58	22
175	-	-	-	16	20	20	35	33	44	35	39	36	16	28	49	80	70	24
200	20	-	-	20	24	24	40	38	50	40	44	39	13	36	53	90	81	25
250	-	-	-	20	-	24	40	38	57	48	50	43	19	36	60	90	104	25
300	-	-	-	20	-	24	40	36,5	72	66	68,5	46	20	44	66	90	124	25

Specification

- Plastic
Technopolymer (Polypropylene PP)
- Reinforced, shock-resistant
- Temperature resistant up to 80 °C
- Black, matte finish
- Hub bushing
Steel, blackened
- Threaded bushing
Brass
- Cover
Plastic, light gray
- Revolving handles
- Plastic, Technopolymer (Polyamide PA)
Black, matte finish
- Spindle steel
Zinc plated, blue passivated
- Keyway P9 DIN 6885 Page 1 → Page 2078
- ISO Fundamental Tolerances → Page 2151

• RoHS

On request

- With revolving handle GN 597.1 → Page 45
- Cover in other colors

Information

Disk handwheels GN 521 have recessed grips at their back.

The cover conceals clamping elements, e.g. countershaft pulleys, as well as protruding and recessed shafts. For mounting, the cover is pushed in by hand. For dismantling, the cover can be raised and taken off by applying moderate pressure in the rim of the cover.

see also...

- Countersunk Washers GN 184 (for Axial Fixing) → Page 1090
- Disk Handwheels GN 524 (Plastic) → Page 256
- Disk Handwheels GN 520.1 (Plastic, Duroplast, Bushing Steel) → Page 257

How to order

GN 521-150-K 14-R

- 1** d₁
- 2** Bore code
- 3** d₂
- 4** Type