



elesa
Original design CT-FG

STAIN
LESS
*

1	2	3																	
d ₁	d ₂	Length l												d ₃	h ₁	h ₂	s	t min.	
		Steel								Stainless steel									
25	M 5	10	16	-	-	-	-	-	10	16	25	-	-	13	24	6	6,5	6	
30	M 6	10	12	16	20	25	30	40	10	16	20	25	30	15,5	28	8	7	8	
30	M 8	16	20	25	30	40	45	-	16	20	25	30	-	15,5	28	8	7	8	

Specification

Handle

- Plastic, polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +130 °C
- Black, matte finish

Threaded bushing

Brass MS

Threaded stud

- Steel ST
- Zinc plated, blue passivated
- Stainless steel AISI 303 NI

RoHS

Wing nuts / Wing screws GN 531.5 clamp and fasten parts easily without tools. Their ergonomic shape and protruding collar make them easy to use.

see also... [ganternorm.com](https://www.ganternorm.com)

- GN 531.1 Wing Screws (Plastic, Threaded Stud Steel, with Protruding Hub)
- GN 532 Wing Nuts (Plastic, Threaded Bushing Brass)
- GN 431 Wing Screws (Stainless Steel)
- GN 432 Wing Nuts (Stainless Steel)
- GN 433 Wing Screws (Stainless Steel)

Technical Information

- Plastic Characteristics
- Stainless Steel Characteristics

How to order (Threaded bushing)

1

2

4

GN 531.5-25-M5-MS

1

2

4

d₁

d₂

Material

How to order (Threaded stud)

1

2

3

4

GN 531.5-30-M6-30-NI

1

2

3

4

d₁

d₂

Length l

Material