




elasa
Original design VCRT.

3 Type

- A Without cover cap
- B With cover cap



1 d ₁	2 d ₂ Thread		2 s H9 Square				d ₃	d ₄ -0,5	h ₁	h ₂	l ₁	l ₂	l ₃ +0,5
32	M 5	M 6	V 5	V 6	-	-	17	11	17	1	8	13,5	6,5
40	M 6	M 8	V 6	-	-	-	17	13	17	1	10	14,5	9,5
50	M 8	M 10	V 6	V 7	-	-	19	16	20	1,2	10	17,5	9,5
63	M 10	M 12	V 6	V 7	V 8	-	22,5	20	21,5	1,3	10	19	9,5
74	M 10	M 12	V 7	V 8	V 9	V 10	26,5	20	24,5	2	15	21	13,5
95	M 16	-	V 8	V 10	-	-	32	18	29,5	4,5	15	26,5	13,5

Specification

- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 130 °C
 - Black, matte finish
- Threaded bushing / square bushing Brass
- Color of the cover cap (matte finish):

●	-
●	DOR
●	DGR
●	DGB
●	DBL
●	DRT
●	DGN
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- RoHS

4

Information

Characteristic of the star knobs GN 5331 is the 5 lobes. They not only give the knobs a specific style but this shape has also enabled the operator to achieve a higher torque.

How to order (Cover cap black)	
1 d ₁	
2 d ₂ (s)	
3 Type	
GN 5331-63-M10-B	

How to order (Cover cap colored)	
1 d ₁	
2 d ₂ (s)	
3 Type	
4 Color of the cover cap	
GN 5331-74-M12-B-DRT	