



elesa
Original design VDS+IR-SST



Inox
Stainless
Steel



2 Bore code

- B** Without keyway
- K** With keyway DIN 6885-1 P9

4 Type

- R** With revolving retractable handle

1 d_1	3 d_2 H7	b	d_3	d_4	d_5	d_6	d_7	h	l_1	l_2	l_3	r	\varnothing Handle
100	10	24	22	20	30	25	27	9	22	34	45	39	15,5
125	12	28	26	24	35	28	31	11	27	39,5	60	49	18
150	14	32	26	24	38	30	34	10	30	44	65	58	22
200	20	39	40	38	50	40	44	13	36	53	90	81	25

Specification

Wheel body

- Plastic, Polypropylene (PP)
- Reinforced, shock-resistant
- Operating temperature 0 °C to +80 °C
- Black, matte finish

Hub bushing

Stainless steel AISI 304

Cover

Plastic, light gray

Retractable handle

- Plastic, Polyamide (PA)
- Black, matte finish
- Retracting mechanism / Spindle
- Stainless steel AISI 303

RoHS

On request

- With safety retractable handle (swivelling)

The handle in the handwheels GN 521.6 is locked in a conical bore in the operating position.

For reversal, it must first be pulled from the cone in axial direction.

A pressure spring holds the handle in both positions. When swung out, it automatically engages again.

The cover conceals clamping elements, e.g. countershaft pulleys, as well as protruding and recessed shafts. For mounting, the cover is pushed in by hand. For dismantling, the cover can be raised and taken off by applying moderate pressure in the rim of the cover.

Technical Information

	Page
Keyways P9 DIN 6885-1	QVX
Cross holes GN 110	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Accessory

GN 184.5 Countersunk Washers (for axial fixing)	QVX
--	-----

How to order

GN 521.6-150-K16-R

- 1** d_1
- 2** Bore code
- 3** d_2
- 4** Type

