



3 Type

- A** Without bore
- E** With threaded blind bore
- D** With threaded through bore
- C** With plain blind bore H7

1

2

2

d₁	d₂ Thread Type D Type E	d₃ H7 Bore Type C	d₄	h₁	h₂	t₁ min.	t₂
40	M 6	-	18	30,5	15	12	13
40	M 8	B 8	18	30,5	15	15	13
50	M 8	-	21	34	17	15	16
50	M 10	B 10	21	34	17	18	16
60	M 10	-	25	39	18	18	20
60	M 12	B 12	25	39	18	22	20

Specification

- Stainless steel AISI 316L
Matte shot-blasted
- *Cross Holes GN 110* → Page 2080
- *ISO Fundamental Tolerances* → Page 2151
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

On request

- Highly polished (PL)

Information

Stainless steel star knobs GN 5335.4 are a special development intended for the food processing machinery industry. The smooth and enclosed areas as well as the large corner radii comply with the requirements of hygiene standards.

see also...

- *Stainless Steel Triangular Knobs GN 5339.5* → Page 602
- *Stainless Steel Star Knobs GN 5334* → Page 574
- *Stainless Steel Wing Nuts GN 834* → Page 618
- *Stainless Steel Star Knobs DIN 6336* → Page 540
- *Stainless Steel Hand Knobs DIN 6335* → Page 582
- *Stainless Steel Three-Lobe Knobs GN 5345* → Page 592

How to order

GN 5335.4-40-M8-E

- 1** d₁
- 2** d₂ (d₃)
- 3** Type