



elesa
Original design IZN.381

1		2			d ₃	d ₄	d ₅	d ₆	d ₇	d ₈	l ₁	l ₂	l ₃	l ₄	l ₅	r
Nominal dimension	Actual dimension	Bore														
32	32	B 6	-	-	15	19,5	21,5	M 4	-	19	26,5	5	16	6,5	9	-
42	42	B 8	-	-	18	29,5	31	M 5	-	28	32	7	17,5	11,5	10,5	-
48	48	B 8	-	-	22	33	34,5	M 5	3	31,6	35,5	8	22	8,5	14	14
52	52	B 10	B 12	-	22	37,5	39	M 5	4	36,2	38,5	8,5	22	12	13,5	15,5
63	63,5	B 10	B 12	B 14	26	48	50,5	M 6	6	45,4	44,5	11	30	10,5	16	19

Specification

Knob

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +100 °C
- Black, shiny finish

Bushing

Steel, blackened

Grub screw

Steel, blackened

Cover

- Plastic, Polyacetal (POM)
- Black, RAL 9005, matte finish
- Orange, RAL 2004, matte finish
- Gray, RAL 7035, matte finish
- Yellow, RAL 1021, matte finish
- Blue, RAL 5024, matte finish
- Red, RAL 3000, matte finish
- Green, RAL 6017, matte finish

- DSW
- DOR
- DGR
- DGB
- DBL
- DRT
- DGN

RoHS

Control knobs GN 526 have a colored cover that conceals protruding or recessed shafts and is suitable for imprinting characters or symbols, if desired.

For assembly, the cover can be pressed on by hand. Disassembly is done by applying light pressure on the edge of the cover.

The combination with scale rings GN 526.1 extends the application possibilities of the control knobs. The scale rings are fastened using the 3 bores on the pitch circle d₈.

see also...	Page
GN 726 Control Knobs (Aluminum)	QVX
GN 726.1 Control Knobs (Aluminum)	QVX

Technical Information

ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

Accessory

GN 526.1 Scale Rings	QVX
GN 826 Clamping Elements (for Adjustable Spindles)	QVX

How to order

GN 526-42-B8-DGR

1	d ₁
2	d ₂
3	Color cover

