



elesa
Original design B.193 p / p-SST

STAIN LESS *

1 2 3

GN 529

d_1	d_2		Length **l**						d_3	h	k
15	M 3	M 4	6	10	16	-	-	-	11	11	9
15	M 5	-	10	16	25	-	-	-	11	11	9
18	M 5	-	10	16	25	40	-	-	13	12	9
22	M 6	-	10	16	20	25	30	40	15	14	10
25	M 6	M 8	16	25	-	-	-	-	19	18	12
30	M 8	-	16	25	40	-	-	-	24	18	12
35	M 8	-	25	40	-	-	-	-	27	23	15

1 2 3

GN 529.5

d_1	d_2		Length **l**						d_3	h	k
15	M 3	M 4	6	10	16	-	-	-	11	11	9
15	M 5	-	10	16	25	-	-	-	11	11	9
18	M 5	-	10	16	25	-	-	-	13	12	9
22	M 6	-	10	16	20	25	30	-	15	14	10
25	M 6	-	16	25	-	-	-	-	19	18	12
30	M 8	-	16	25	40	-	-	-	24	18	12

Specification

Knob
Plastic, phenolic resin (PF)
- Operating temperature -20 °C to +110 °C
- Black, shiny finish

GN 529
Threaded stud
Steel
Black, shiny finish

GN 529.5
Threaded stud
Stainless steel AISI 303

RoHS

The surface quality of the knurled nut GN 529 / GN 529.5 is of a sufficiently high standard to meet the highest requirements. The flash mark is not visible.

Technical Information	Page
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order (Threaded stud steel)
1 2 3
GN 529-25-M8-16

1	d_1
2	d_2
3	Length **l**

How to order (Threaded stud stainless steel)
1 2 3
GN 529.5-18-M5-16

1	d_1
2	d_2
3	Length **l**