



- 3 Type**
- A Without bore (unmachined)
 - C With blind bore H7
 - D With threaded through bore
 - E With threaded blind bore

1 d_1	2 d_2 Thread Type E	Type D Type E	2 d_3 H7 Bore Type C	$d_4 +0,5$	$h_1 -1$ Type A	Type C Type D Type E	$h_2 \approx$	t_1 min.	t_2
40	M 6	M 8	B 8	14	26	25	12,5	15	13
50	M 8	M 10	B 10	18	33	32	16	18	16
60	M 10	M 12	B 12	20	41	40	20	22	20
70	M 12	M 16	B 16	25	47	46	23	28	20

Specification

- Aluminum
 - Matte finish (tumbled) **MT**
 - Flash mark not visible
 - Polished **PL**
- Type **A** (without bore)
Only available with a matte finish (MT)
- *Cross Holes GN 110* → Page 2080
- *ISO Fundamental Tolerances* → Page 2151
- RoHS

Information

Star knobs GN 5336 are forged, therefore a close grain structure is maintained providing a high tensile strength and a smooth surface.

Original ELESA design, now produced in metal in agreement with ELESA S.p.A.

How to order (Without bore)

GN 5336-60-A-MT

1	d_1
3	Type
4	Finish

How to order (With bore)

GN 5336-50-M10-E-MT

1	d_1
2	d_2 (d_3)
3	Type
4	Finish

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4