





elesa
Original design VB.639 / VB.639 FP

STAIN LESS *

3 Type

E With threaded blind bore
D With threaded through bore

GN 5330

1 d_1	2 d_2 Type E		2 d_3 Type D		d_4	d_5	d_6	h_1	h_2	Length l	t min.
45	M 6	-	M 6	-	19	8	9	25	22,5	12	13
45	M 8	-	M 8	-	19	11	10	25	22,5	12	13
63	M 8	-	-	-	26	-	-	28	25	-	15
63	M 10	-	M 10	M 12	26	16	13	28	25	21	17
80	M 10	M 12	M 12	-	32	18	17	35	30	25	17
100	M 12	M 14	M 16	-	36	20	19	42	36	31	20
130	M 16	-	M 16	-	43	24	22	47	40	34	22

GN 5330.5

1 d_1	2 d_2 Type E	d_4	h_1	h_2	t min.
45	M 6	19	25	22,5	12
63	M 8	26	28	25	15
80	M 10	32	35	30	17
100	M 12	36	42	36	20
130	M 16	43	47	40	22

Specification

Knob
Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature** -30 °C to +130 °C
- Black, matte finish

GN 5330
Threaded bushing
Brass

GN 5330.5
Threaded bushing
Stainless steel AISI 303

RoHS

On request

- With bore H9

The shape and dimensions of three-lobed knobs GN 5330 / GN 5330.5 allow a high amount of torque to be applied.

see also...	Page
GN 5345 Three-Lobed Knobs	QVX

Technical Information

ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order (Threaded bushing brass)
1 2 3
GN 5330-80-M12-E

1	d_1
2	d_2 (d_3)
3	Type

How to order (Threaded bushing stainless steel)
1 2 3
GN 5330.5-63-M8-E

1	d_1
2	d_2
3	Type