



elesa
Original design VC.192-B / VC.254

- 3 Type**
E With threaded blind bore
D With threaded through bore

d ₁	d ₂		GN 5337.5		d ₃	d ₄	h ₁		h ₂ +1	h ₃	t ₁ min.	t ₂
	GN 5337 Type E	Type D	Type E	Type E			Type D	Type E				
32	M 6	-	-	M 6	-	19	-	23	11	-	12	-
40	M 6	M 8	M 8	M 8	14	21	28	27	12	1,5	13	18
50	M 8	M 10	M 10	M 10	16	25	34	33	14	1,5	17	22
60	M 10	M 12	M 12	M 12	17	27	38	37	17	1,5	20	26
70	M 12	-	M 12	-	17	30	45	44	20	1,5	20	26
85	M 16	-	M 16	-	24	35	56	55	30	2	22	35

Specification

Knob

- Plastic, Phenolic resin (PF)
- Operating temperature -20 °C to +110 °C
- Black, shiny finish

GN 5337

Threaded bushing
Brass

GN 5337.5

Threaded bushing
Stainless steel AISI 303

RoHS

Star knobs GN 5337 / Gn 5337.5 meet highest quality requirements. Due to a special manufacturing process the mould parting line can be avoided.

see also...

	Page
GN 5337.2 Star Knobs (Plastic, Threaded Bushing Brass / Steel)	QVX
GN 5337.4 Star Knobs (Plastic, Threaded Bushing Stainless Steel)	QVX

Technical Information

Plastic Characteristics	QVX
-------------------------	-----

How to order (Threaded bushing brass)

GN 5337-40-M8-D

1	d ₁
2	d ₂
3	Type

How to order (Threaded bushing stainless steel)

GN 5337.5-50-M10-E

1	d ₁
2	d ₂
3	Type

