



**3 Type**

- A** Only with retaining ring
- H** With retaining cable
- K** With ball chain

<b>1</b> $d_1$	<b>2</b> $d_2$	$d_3$	$h_1$	$h_2$	$h_3$	$r \approx$	$s$	$t$ min.
40	M 8	14	24	12	3,2	22,3	2,8	15
50	M 10	18	30	17	3,9	29,6	3,2	18
60	M 12	20	38	20	3,9	30,7	3,2	22

**Specification**

- Knob  
Stainless steel AISI 316L  
- Hub welded  
- Matte, shot blasted
- Threaded bushing  
Stainless steel AISI 304
- Retaining ring GN 111.6  
Stainless steel AISI 301
- Ball chain GN 111.5 (Type K)  
Stainless steel AISI 301
- Retaining cable GN 111.2 (Type H)  
Stainless steel  
Coated with clear plastic
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**On request**

- Ball chains / retaining cables with other lengths
- With spiral retaining cable GN 111.4
- Other GN / DIN standards with loss protection

**Information**

Stainless steel star knobs GN 5334.13 can be captive-attached to a base element with the help of a ball chain or a retaining cable.

The star knobs are supplied ready assembled (with retaining ring and ball chain or retaining cable).

Original ELESA design, now produced in metal in agreement with ELESA S.p.A.

**see also...**

- *Stainless Steel Ball Chains GN 111.5* → Page 1174
- *Stainless Steel Retaining Cables GN 111.2* → Page 1176
- *Spiral Retaining Cables GN 111.4* → Page 1175
- *Stainless Steel Retaining Rings GN 111.6* → Page 1179
- *Further Star Knobs with Loss Protection GN 111.7* → Page 2084

**How to order**

**GN 5334.13-40-M8-H**

<b>1</b>	$d_1$
<b>2</b>	$d_2$
<b>3</b>	Type