

STAIN LESS ★

1 d_1	2 d_2		3 Length l				d_3	d_4	d_5	h_1	h_2	h_3	h_4 Stroke	t min.
40	M 6	M 8	20	25	32	40	13,5	18	13,5	30	14	7	2,5	11
50	M 8	M 10	25	32	40	50	16	22	16,5	34	15	8	3,5	14

Specification

4

Knob
Plastic, Polyamide (PA)
- Glass fiber reinforced
- Black, matte finish
- Annular gear, zinc die casting

Insert

• Steel, blackened	**ST**
• Stainless steel AISI 303	**NI**

Cover cap
Plastic, Polypropylene (PP)
Black, RAL 9005, matte finish

Operating temperature -30 °C to +130 °C

RoHS

On request

- Cover caps in other colors

Safety star knobs GN 5337.3 are most suitable for applications where an accidental or inconsiderate loosening or adjusting of the knob may lead to accidents.
In non-operative condition, the star knob is not linked with the threaded bushing, i.e. the knob can be turned easily.
Only after axial pushing of the star knob, the two serrations get engaged so that the knob can be untightened resp. tightened.
Atfer releasing, the two serrations are disengaged by a spring.

see also...	Page
GN 312 Safety Tension Levers	QVX
GN 604.2 Safety Hand Levers	QVX

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order (Threaded bushing)
1 2 4
GN 5337.3-40-M8-ST

1	d_1
2	d_2
4	Material

How to order (Threaded stud)
1 2 3 4
GN 5337.3-50-M10-40-NI

1	d_1
2	d_2
3	Length l
4	Material