



d₁		d₂	d₃ H9	d₄	h₁	h₂	t₁	t₂
Nominal dimension	Actual dimension	Thread	Bore				min.	min.
32	31	M 5	-	15	24	11,5	10	-
32	31	M 6	-	15	24	11,5	12	-
40	39,5	M 6	B 6	17	26,5	12,5	12	14
40	39,5	M 8	-	17	26,5	12,5	13	-
50	50	M 8	B 8	20	33	16	20	20
50	50	M 10	-	20	33	16	18	-
60	61	M 10	B 10	23	39	18,5	20	25
60	61	M 12	-	23	39	18,5	20	-
70	70	M 12	-	24	42	20,5	20	-
70	70	M 14	-	24	42	20,5	20	-

Specification

- Plastic
Technopolymer (Polypropylen PP)
- Reinforced, shock-resistant
- Temperature resistant up to 90 °C
- Black, RAL 9005, matte ● **SW**

- Bushing
Brass

- Color of the cover cap (matte finish):
Black, RAL 9005 ● -
Orange, RAL 2004 ● **DOR**
Gray, RAL 7035 ● **DGR**
Yellow, RAL 1021 ● **DGB**
Blue, RAL 5024 ● **DBL**
Red, RAL 3000 ● **DRT**
Green, RAL 6017 ● **DGN**

- ISO Fundamental Tolerances → Page 2151
- Cross Holes GN 110 → Page 2080
- Plastic Characteristics → Page 2158
- RoHS

Information

The unique profile on the rim (small squares) of the knurled knobs GN 534 is characteristic of its form and the function.

see also...

- Control Handwheels GN 735 → Page 280
- Knurled Knobs GN 7336 → Page 626
- Knurled Knobs GN 4534 (Softline) → Page 624
- Knurled Knobs GN 534 with Loss Protection GN 111.7 → Page 2084

How to order (Cover cap black) 1 d₁ 2 d₂ (d₃) 3 Color (Knob)	1	d ₁
	2	d ₂ (d ₃)
	3	Color (Knob)

How to order (Cover cap colored) 1 d₁ 2 d₂ (d₃) 3 Color (Knob) 4 Color (Cover cap)	1	d ₁
	2	d ₂ (d ₃)
	3	Color (Knob)
	4	Color (Cover cap)