



3 Type

- E** With threaded blind bore
- C** With blind bore H7

1 d_1		2 d_2 Thread		2 d_3 H7 Bore	d_4	$h_1 \approx$	$h_2 \approx$	t min.
32		M 5	M 6	B 6	12	21	10	12
40		M 6	M 8	B 8	14	24	12	15
50		M 8	M 10	B 10	18	30	16,5	18
60		M 10	M 12	B 12	20	37,5	20	22

Specification

- **GN 5334**
Stainless steel AISI 304
- **GN 5334.4**
Stainless steel AISI 316L

This information applies to both standards:

- Knob drawn from stainless steel sheet
- Hub welded
- Matte shot-blasted

- *Cross Holes GN 110* → Page 2080
- *ISO Fundamental Tolerances* → Page 2151
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

Information

The original ELESA design with 5 recess grips is typical for star knobs GN 5334 / GN 5334.4.

This form gives these grips an appealing look and additionally allows a high torque to be achieved.

Original ELESA design, now produced in metal in agreement with ELESA S.p.A.

see also...

- *Triangular Knobs GN 5339.5 (Stainless Steel)* → Page 602
- *Star Knobs GN 5335 (Stainless Steel)* → Page 578
- *Wing Nuts GN 834 (Stainless Steel)* → Page 618
- *Star Knobs DIN 6336 (Stainless Steel)* → Page 540
- *Hand Knobs DIN 6335 (Stainless Steel)* → Page 582
- *Three-Lobe Knobs GN 5345 (Stainless Steel)* → Page 592
- *Star Knobs GN 5334 (Stainless Steel, with Loss Protection GN 111.7)* → Page 2084

How to order (Stainless steel AISI 304)		1 d_1
GN 5334-50-M10-E		2 d_2 (d_3)
		3 Type

How to order (Stainless steel AISI 316L)		1 d_1
GN 5334.4-40-B8-C		2 d_3 (d_2)
		3 Type