Knurled Nuts / Knurled Screws

Stainless Steel



STAINLESS **

1 d_1	2 d_2	3 Length l			d_3	h	k	t min.
20	M 5	10	16	-	14	13	8,5	8
24	M 6	16	20	25	16	15	10,5	9
28	M 8	16	20	30	18	17	12,5	10

Specification

4

Stainless steel precision casting AISI 304

- Matte shot-blasted finish **MT**
- Highly polished **PL**

RoHS

The knurling of the knurled nuts GN 536 allows a use in an environment with hygienic requirements.

see also...	Page
DIN 6303 Stainless Steel Knurled Nuts	QVX
DIN 466 Knurled Nuts	QVX

Technical Information

Stainless Steel Characteristics	QVX

How to order (Internal thread)

1 2 4

GN 536-20-M5-MT

1	d_1
2	d_2
3	Finish

How to order (Threaded stud)

1 2 3 4

GN 535-28-M8-20-MT

1	d_1
2	d_2
3	Length l
4	Finish