



Rostfrei
 Inch sizes available
 Inox Stainless Steel

3 Type

- A** without bore
- E** with threaded blind bore
- D** with threaded through bore
- C** with plain blind bore H7

1 d_1	2 d_2 Thread Type D Type E	2 d_3 H7 Bore Type C	d_4	h_1	h_2	t_1 min.	t_2
40	M 6	-	18	30,5	15	12	13
40	M 8	B 8	18	30,5	15	15	13
50	M 8	-	21	34	17	15	16
50	M 10	B 10	21	34	17	18	16
60	M 10	-	25	39	18	18	20
60	M 12	B 12	25	39	18	22	20

Specification

- **GN 5335**
Stainless Steel AISI 303 (A1)
- matte shot-blasted —
- highly polished **PL**
(only Type D and E)
- Cross holes GN 110 → Page 1422
- ISO-Fundamental tolerances → Page 1479
- Stainless Steel characteristics → Page 1489
- **RoHS**

Information

Stainless Steel-Star knobs GN 5335 are a special development intended for the food processing machinery industry. The smooth and enclosed areas as well as the large corner radii comply with the requirements of hygiene standards.

see also...

- Stainless Steel-Star knobs GN 5334 → Page 414
- Stainless Steel-Wing nuts GN 834 → Page 436
- Stainless Steel-Knurled nuts GN 536 → Page 452

How to order	1 d_1
	2 d_2
GN 5335-50-M10-D-PL	3 Type
	4 polished