



1.1

1.2

1.3

1.4

¹ d ₁	² d ₂	d ₃	d ₄	h ₁	h ₂	t min.
40	M 6	18	18,8	26	15	12
40	M 8	18	18,8	26	15	15
50	M 8	21	21,8	30	17	15
50	M 10	21	21,8	30	17	18

2.1

Specification

- Stainless steel AISI 316L
 - Matte finish (Ra < 0,8 µm) **MT**
 - Polished finish (Ra < 0,8 µm) **PL**
- Sealing ring
 - H-NBR **H**
Temperature resistant -25 °C to +150 °C
 - EPDM **E**
Temperature resistant -40 °C to +120 °C
 - Blue
 - Hardness 85±5 Shore A
 - FDA compliant
- Plastic Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

Accessory

- Sealing Rings GN 7600 → Page 1596

On request

- with FKM sealing ring (Fluorine rubber) **F**

Information

Three-lobed knobs GN 5445 are intended for use in hygienic areas. The sealed mounting surface enables fastening without dead spaces. The high quality finish as well as the large corner radii and closed surfaces prevent adherence of dirt and facilitate cleaning.

see also...

- Product Family *Hygienic Design* → Page 16
- Adjustable Hand Levers GN 305 (Stainless Steel, *Hygienic Design*) → Page 442
- Star Knobs GN 5435 (Stainless Steel, *Hygienic Design*) → Page 581

2.2

2.3

2.4

How to order

¹ d ₁	1	d ₁
² d ₂	2	d ₂
³ Finish	3	Finish
⁴ Material (Sealing ring)	4	Material (Sealing ring)

GN 5445-40-M8-PL-H