



- 3 Type**
- A Without bore (unmachined)
 - C With blind bore H7
 - D With threaded through bore
 - E With threaded blind bore

1 d ₁	2 d ₂ Thread Type E		Type D	2 d ₃ H7 Bore Type C	d ₄ +0,5-	h ₁ -1 Type A	Type C Type D Type E	h ₂ ≈	t ₁ min.	t ₂
40	M 6	M 8	M 8	B 8	14	26	25	12,5	15	13
50	M 8	M 10	M 10	B 10	18	33	32	16	18	16
60	M 10	M 12	M 12	B 12	20	41	40	20	22	20
70	M 12	M 16	M 16	B 16	25	47	46	23	28	20

Specification

Aluminum

- Matte finish, tumbled
- Flash mark not visible
- Polished
- (only type C / D / E)



MT
PL

RoHS

Star knobs GN 5336 are forged, therefore a close grain structure is maintained providing a high tensile strength and a smooth surface. Original ELESA design, now produced in metal in agreement with ELESA S.p.A.

see also...

	Page
DIN 6336 Star Knobs (Aluminum)	QVX
GN 5334 Star Knobs (Stainless Steel)	QVX
GN 5337.4 Star Knobs (Plastic, Bushing Stainless Steel)	QVX

Technical Information

Cross holes GN 110	QVX
ISO Fundamental Tolerances	QVX

How to order (Without bore)

GN 5336-60-A-MT

- 1** d₁
- 2** Type
- 3** Finish

How to order (With bore)

GN 5336-50-M10-E-MT

- 1** d₁
- 2** d₂ (d₃)
- 3** Type
- 4** Finish

