



| ¹ d ₁ | ² d ₂ | d ₃ | d ₄ | h ₁ | h ₂ | t _{min} |
|-----------------------------|-----------------------------|----------------|----------------|----------------|----------------|------------------|
| 40 | M 6 | 18 | 18,8 | 26 | 15 | 12 |
| 40 | M 8 | 18 | 18,8 | 26 | 15 | 15 |
| 50 | M 8 | 21 | 21,8 | 30 | 17 | 15 |
| 50 | M 10 | 21 | 21,8 | 30 | 17 | 18 |

Specification

Three-lobed knob

Stainless steel AISI 316L

- Matte finish (Ra < 0.8 µm)
- Polished finish (Ra < 0.8 µm)

MT
PL

Sealing ring

- HNBR **H**
Operating temperature -25 °C to +150 °C
- EPDM **E**
Operating temperature -40 °C to +120 °C
- FKM **F**
Operating temperature -5 °C to +200 °C
- FDA compliant material
- Blue
- Hardness 85±5 Shore A

RoHS

Three-lobed knobs GN 5445 are intended for use in hygienic areas. The sealed mounting surface enables fastening without dead spaces. The high quality finish as well as the large corner radii and closed surfaces prevent adherence of dirt and facilitate cleaning.

see also...

| | Page |
|--|------|
| GN 5435 Star Knobs (Edelstahl, Hygienic Design) | QVX |
| GN 305 Adjustable Hand Levers (Edelstahl, Hygienic Design) | QVX |

Technical Information

| | |
|---------------------------------|-----|
| Product Family Hygienic Design | QVX |
| Plastic Characteristics | QVX |
| Stainless Steel Characteristics | QVX |

Accessory

| | |
|-----------------------|-----|
| GN 7600 Sealing Rings | QVX |
|-----------------------|-----|

How to order

| |
|--------------------------------------|
| ¹ d ₁ |
| ² d ₂ |
| ³ Finish |
| ⁴ Material (Sealing ring) |

GN 5445-40-M8-PL-H

