



ELESA original design VCT.AE-VO

3 Type

E with cover cap
(threaded blind bore)

1

2

d ₁	d ₂	d ₅	d ₆	h ₁	h ₂	t ₁
25	M 5	13	8	19	8	10
32	M 6	15	10	23	10	12
40	M 8	17	13	27	12	18
50	M 10	19	15	32	14	20

Specification

- Plastic
Technopolymer (Polyamide PA)
- glass fiber reinforced
- self extinguishing
- temperature resistant up to 150 °C
- black, matte
- Bushing brass
- *Plastic characteristics* → Page 1483
- RoHS

4

SV



Information

Star knobs GN 5337.2 version SV are produced from a plastic material, which according to UL 94 V-O is classified as a self extinguishing material. This classification to UL 94 V-O (Underwriters Laboratories) determines the resistance of a plastic material to fire. This comprises a test on a piece of plastic material of a specific form and dimensions in a vertical position to be set alight, whereby the flame according to V-O must extinguish itself without burning droplets developing.

see also...

- *Star knobs GN 5337.2 (Bushing brass / steel)* → Page 406
- *Star knobs GN 5337.4 (Bushing Stainless Steel)* → Page XYZ
- *Softline-Star knobs GN 5337.6* → Page 408
- *Star knobs GN 5337.2 with loss protection GN 111.7* → Page 1426

How to order

1	d ₁
2	d ₂
3	Type
4	Material

GN 5337.2-40-M6-E-SV

