



- 2 Bore**
B Without keyway
K with keyway

Length l	d ₁ H7 Bore	d ₂	h	b P9	t
75	16	32	24	5	17,3
90	18	34	26	6	19,7
110	20	36	30	6	21,7
135	22	42	32	6	23,7
165	24	44	36	8	25,7

Specification

- Body
Cast iron (GGG)
- Hub machined, flash
- Ground, shot-blasted
- Handle
Steel, blackened
- Indexing pin
Steel, hardened
- [Keyway P9 DIN 6885 Page 2 → Page 2079](#)
- [ISO Fundamental Tolerances → Page 2151](#)
- RoHS

Information

Indexing cranked handles GN 558 are for positioning mechanisms. Standard machine elements for positioning of spindles:

see also...

- [Indexing Mechanisms GN 200 → Page 352](#)
- [Indexing Levers GN 215 → Page 358](#)
- [Adjustable Knobs GN 700 \(with Stepless Positioning\) → Page 356](#)

How to order

GN 558-75-K16

- | | |
|---|----------------|
| 1 | Length l |
| 2 | Bore code |
| 3 | d ₁ |

