GN 5337.4 Star Knobs with Threaded Stud

Plastic, Threaded Stud Stainless Steel





elesa

Original design VC.692.SST-p

STAIN LESS *



1 d_1	2 d_2	3 Length l							d_3	h_1	$h_2 \approx$
25	M 4	6	10	-	-	-	-	-	12	20	10
25	M 5	10	16	20	25	-	-	-	12	20	10
25	M 6	10	16	20	25	30	35	-	12	20	10
32	M 6	10	16	20	30	35	-	-	14	22,5	12,5
32	M 8	16	20	25	30	40	-	-	14	22,5	12,5
40	M 6	10	20	30	40	-	-	-	15	26	14
40	M 8	16	20	25	30	35	40	45	15	26	14
50	M 8	16	20	25	30	35	40	50	18	31	17
50	M 10	20	30	40	50	-	-	-	18	31	17
60	M 10	20	30	40	50	-	-	-	21	36,5	21
60	M 12	30	40	50	-	-	-	-	21	36,5	21

Specification

Knob

Plastic, Polyamide (PA)

- Glass fiber reinforced
- Operating temperature -30 °C to +130 °C
- Black, matte finish

Threaded stud

Stainless steel AISI 303

RoHS

On request

- Threaded stud
  Steel, zinc plated, blue passivated finish

Furthermore the underside of the knob GN 5337.4 is not recessed or hollowed. This means that if they are fitted with a stainless steel bushing they will meet the standards and requirements for hygiene applications.

see also...	Page
GN 5337.5 Star Knobs (Phenolic Resin, Threaded Stud Stainless Steel)	QVX
GN 5337.4 Star Knobs (Threaded Bushing Stainless Steel)	QVX
GN 5337.4 Star Knobs (with Loss protections GN 111.7)	QVX

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

1 2 3

GN 5337.4-25-M6-10

1	d_1
2	d_2
3	Length l