



4 Type
SU Lock with different combinations

1 d_1	2 d_2	3 Length l	d_3	h_1	$h_2 \approx$	t
63	M 6	-	23	44	17	18
63	M 8	20	23	44	17	18
63	M 10	20	23	44	17	20

Specification

- Knob
 Plastic
 Technopolymer (Polyamide PA-HP)
 - Glass fiber reinforced
 - Temperature resistant up to 100 °C
 - Black, matte finish
- Cover flange plastic with knob ultrasonically welded
- Threaded bushing
 Brass
- Threaded stud
 Steel
 Zinc plated, blue passivated
- Lock mechanism
 Zin die casting
- Key
 Brass, nickel plated with handle in plastic
- *Plastic Characteristics* → Page 2158
- RoHS

Information

Safety star knobs GN 5337.9 are designed to prevent unauthorised use. To engage and release, the key must be inserted and turned by 180°, creating a formlock between the handle and the threaded bushing or screw. Turning the key back by 180° will release the connection. The key can be inserted and pulled off in both end positions. Two keys per star knob are included with the delivery.

see also...

- *Safety Star Knobs GN 5337.8* → Page 568

How to order (Threaded bushing)	1 d_1
	2 d_2
	4 Type
	GN 5337.9-63-M6-SU

How to order (Threaded stud)	1 d_1
	2 d_2
	3 Length l
	4 Type
GN 5337.9-63-M10-20-SU	