



- 2

Type
- A

Closed type
- B

Open ended type, mounting from the back (threaded blind bore)
- C

Open ended type, mounting from the operator's side

1

$l_1 \pm 0,25$	a_1	a_2	a_3	b_1	b_2	d_1	d_2	h_1	h_2	h_3	h_4	h_5	l_2	$l_3 \pm 0,2$	l_4	l_5	l_6	l_7	t_1 min.	t_2 min.	t_3
162	38	19	40	25	28	M 8	8,3	55	57	36	38	28	128	140	8	22	10	20	12	16	8

Specification

3

Aluminum

Powder coated

Black, RAL 9005, textured finish

Silver, RAL 9006, textured finish

SW

SR

Cover cap (Type C)

Plastic

Black for SW

Light gray for SR

Load Rating Information → Page 2106

RoHS

Information

A special characteristic of the cabinet U-handles GN 559 is the thumb rest pad on the front of the leg. At the same time the extended leg offers an open ended version with wide access.

The fastening bores of type C are closed by a cover cap following the handle installation. The cover cap is included in the delivery contents.

Cabinet U-handles GN 559 are known for their high stability. They are fixed by two M8 screws whereby type A offers two alternative hole centers (l_2 or l_3).

How to order	1	l_1
GN 559-162-B-SW	2	Type
	3	Finish