



elesa
Original design L.652



1 Length l		2 d ₁ H9 Bore		2 d ₂ Thread		d ₃	h ₁	h ₂	s Square	t min.
Nominal dimension	Actual dimension									
40	41	-	M 5	-	28	18,5	13	16		
40	41	B 6	M 6	9	28	18,5	13	16		
55	56,5	-	M 5	-	33	21,5	15	15		
55	56,5	B 6	M 6	10	33	21,5	15	18		
55	56,5	-	M 8	10	33	21,5	15	18		
67	68,5	B 6	-	11	37	24,5	16,5	20		
67	68,5	B 8	M 8	11	37	24,5	16,5	20		
67	68,5	-	M 10	-	37	24,5	16,5	20		
80	82	B 6	-	14	41,5	25	20	25		
80	82	B 8	M 8	14	41,5	25	20	25		
80	82	-	M 10	14	41,5	25	20	25		
80	82	-	M 12	14	41,5	25	20	18		
93	94	B 6	-	15	46	28,5	21	25		
93	94	-	M 10	15	46	28,5	21	25		
93	94	-	M 12	15	46	28,5	21	18		

Specification

Handle

- Plastic, Polyamide (PA)
- Glass fiber re-inforced
 - Operating temperature -30 °C to +130 °C
 - Black, matte finish

Threaded bushing

Brass

RoHS

On request

- T-Handles in orange or red

T-handles GN 563 can be used on operating handles as well as on clamping fixtures. These handles lend themselves ideally for very high manual clamping forces.

see also...

	Page
GN 563.2 T-Handles (Aluminum)	QVX
GN 563.1 T-Handle Screws (Plastic)	QVX

Technical Information

ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

How to order

GN 563-80-B8

1 Length l

2 d₁ (d₂)