


SOFT



1

2

b	Length l ±0,25	a	d ₁	d ₂	h	r	t min.
25	112	16	M 6	10	50	5	10
25	128	16	M 6	10	54	7	10
25	160	16	M 6	10	54	9	10
25	192	16	M 6	10	54	9	10
35	160	25	M 8	17	68	12,5	12
35	192	25	M 8	17	68	12,5	12
35	300	25	M 8	17	68	12,5	12

Specification

- Sheathing
 - Thermoplastic polyurethane (TPU)
 - Black, textured matte finish
 - Elastic, 65±5 Shore A
 - Temperature resistant up to 70 °C
 - Abrasion-resistant
 - Insulating
 - Weather-proof
- Handle core
 - Stainless steel AISI 303
 - Round (for size b = 25)
 - Aluminum
 - Elliptical (for size b = 35)
- Load Rating Information → Page 2106
- Elastomer Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

On request

- Other colors

Information

The shock absorbing casing of the GN 564 cabinet U-handles made of thermoplastic polyurethane (TPU) offers protection from injuries, while its elliptical shape gives it a nice hold.

The stainless steel core and the aluminum core guarantee a high basic durability of the handle.

see also...

- Product Family Softline → Page 18
- Cabinet U-Handles GN 565 (Aluminum) → Page 106
- Cabinet U-Handles GN 725 (Plastic) → Page 110

1.1

1.2

1.3

2.1

2.2

2.3

2.4

How to order

1 2
GN 564-25-128

1

b

2

Length l

