



STAIN
LESS

¹ d ₁	² d ₂	d ₃	h	k	t min.
20	M 5	14	13	8,5	8
24	M 6	16	15	10,5	9
28	M 8	18	17	12,5	10

Specification

Stainless steel precision casting AISI 304

- Matte shot-blasted finish
- Highly polished

³

MT
PL

RoHS

The knurling of the knurled nuts GN 536 allows a use in an environment with hygienic requirements.

see also...	Page
DIN 6303 Stainless Steel Knurled Nuts	QVX
DIN 466 Knurled Nuts	QVX

Technical Information

Stainless Steel Characteristics	QVX
---------------------------------	-----

How to order (Internal thread)	¹ d ₁
	² d ₂
	³ Finish
GN 536-20-M5-MT	

How to order (Threaded stud)	¹ d ₁
	² d ₂
	³ Length l
	⁴ Finish
GN 535-28-M8-20-MT	