



1

2

Length l	d <sub>1</sub> H9 Bore	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub> ≈	t min.	Ø Handle
50	B 6	15	18	22,5	29,5	18,5	12,5	35	16	14
64	B 8	15	20	26,5	31,5	17,5	13,5	45	18	16
80	B 10	18	24	30	37	23,5	13,5	60	23	18
100	B 12	18	24	33,5	40,5	25	14	65	22	22
130	B 14	26	34	39	49	34	15	65	28	22
160	B 16	26	34,5	44	54,5	36	18	80	28	24

## Specification

- Body  
Plastic  
Technopolymer (Polyamide PA)
  - Glass fiber reinforced
  - Temperature resistant up to 90 °C
  - Black, matte finish
- Hub bushing  
Steel, blackened
- Revolving handles
  - Plastic, Technopolymer  
Black, matte finish
  - Spindle steel  
Zinc plated, blue passivated
- Cross Holes GN 110 → Page 2080
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- RoHS

## Information

Cranked handles GN 570.2 are connected to a shaft by means of a cross pin.

Owing to the small, non-protruding steel bushing, these cranked handles are lower priced than GN 570.

see also...

- Cranked Handles GN 471 (Aluminum) → Page 286
- Cranked Handles GN 471.1 (Zinc Die Casting) → Page 286

How to order

GN 570.2-80-B10

1 Length l

2 d<sub>1</sub>