



View of magnetic surface



2

d ₁	d ₂	h	Nominal magnetic forces in N
10	8	9	4
18	14	8	10
25	22	8,5	14
30	28,5	8,5	27
36	32,5	8,5	35
40	36	8	35

Specification

1

3

- Material of the magnet
NdFeB **ND**
Neodymium, iron, boron
Temperature resistant up to 80 °C
- Housing
Plastic
 - White, RAL 9003 ○ WS
 - Gray, RAL 7040 ● GR
 - Black, RAL 9004 ● SW
 - Red, RAL 3031 ● RT

• RoHS

On request

- Other colors
- Magnet material hard ferrite
- With custom imprint

Information

Magnets GN 53.1 work in combination with the flat, rectangular plastic housing as a system for holding documents, templates, drawings etc. that are used in technical environments.

The neodymium magnets used are characterized by a high magnetic force.

see also...

- *More Information to Magnets* → Page 2028

How to order

GN 53.1-ND-30-RT

1	Material of the magnet
2	d ₁
3	Color