Cranked Handles with Retractable Handle

Plastic, Hub Bushing Steel



elesa
Original design MT-AT+IR

1 Length l	2 d_1 H9	d_2	d_3	d_4	h_1	h_2	h_3	h_4	h_5 ≈	t min.	Ø Handle
64	B 8	15	20	26,5	31,5	17,5	13,5	14	45	18	16
80	B 10	18	24	30	37	23,5	13,5	14	60	23	18
100	B 12	18	24	33,5	40,5	25	14	18,5	65	22	22
130	B 14	26	34	39	49	34	15	18,5	65	28	22
160	B 16	26	34,5	44	54,5	36	18	18,5	80	28	24

Specification

Body
Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature 0 °C to +90 °C
- Black, matte finish

Hub bushing
Steel, blackened

Retractable handle
Plastic, Polyamide (PA)
- Black, matte finish
- Retractable mechanism
  Steel, blackened

RoHS

Cranked handles GN 570.3 are connected to a shaft by means of a cross pin and are used for applications where the handpiece has to stay occasionally in its retracted position.
The handle is pulled out of its taper seating in the direction of the arrow and then titled.
A pressure spring locks the handle in both end positions.
A positive lock is achieved in the operating position by way of a taper seating.

see also...	Page
GN 471.3 Cranked Handles with Retractable Handle (Aluminum)	QVX
GN 472.3 Cranked Handles with Retractable Handle (Aluminum)	QVX

Technical Information	
Cross holes GN 110	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

How to order		
GN 570.3-64-B8 (1 2)	1	Length l
	2	d_1