



**2 Bore code**

- B** Without keyway
- K** With keyway

**4 Type**

- A** Without handle
- D** With revolving handle

**1** **3**

d <sub>1</sub>	d <sub>2</sub> H7 Bore		d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub>	b	l <sub>1</sub> -0,5	l <sub>2</sub> -0,5	l <sub>3</sub> ≈	l <sub>4</sub> ≈	r	Ø Handle	No. of spokes
100	10	12	25	19	28	15	-	23	28	54,5	37	16	3
125	12	14	24	20	30	18	1	25	35	67	47	20	3
140	14	-	32	24	36	20	3	26	35	67	53	20	3
160	14	16	32	24	37	22	5	28	40	83	59	25	3
200	18	20	40	31	45	24	4	33	45	83	76	25	3
250	24	-	49	38	56	29	7	36	58	105,5	98	32	3
300	26	-	58	47	70	32	2	40	65	105,5	113	32	3

**Specification**

- Plastic  
Duroplast (PF)
  - Reinforced
  - Temperature resistant up to 110 °C
  - Black, shiny finish
  - Moulding flash removed and polished
- Hub bushing  
Steel, blackened
- Threaded bushing  
Brass
- Revolving handles DIN 98  
Plastic, Technopolymer  
Black, matte finish
- *Keyway P9 DIN 6885 Page 1 → Page 2078*
- *ISO Fundamental Tolerances → Page 2151*
- *Plastic Characteristics → Page 2158*
- RoHS

**Information**

Bore diameter and plane face of the steel bushing in the handwheels GN 555 are machined only **after** pressing and clamped at the ring, ensuring a good concentricity and plane run of the wheel rim. The accurate fitting bore with the plane face perpendicular to the bore diameter is guaranteed.

Handwheels GN 555 are also available without hub bore.

see also...

- *Countersunk Washers GN 184 (for Axial Fixing) → Page 1090*

**How to order**

**GN 555 - 160 - K 16 - D**

- 1** d<sub>1</sub>
- 2** Bore code
- 3** d<sub>2</sub>
- 4** Type