



1.1
1.2
1.3
1.4

Length l	d ₁ H7 Bore	d ₂ Thread		h ₁	h ₂	s Square	t min.
55	B 6	M 6	M 8	33	22	14	12
67	B 8	M 8	-	37	25	16	16
80	B 8	M 8	M 10	41	26	20	16

2.1
2.2
2.3

Specification

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish
 - Silver, RAL 9006, textured finish
 - Plain
 - Tumbled
 - Flash mark not visible
- ISO Fundamental Tolerances → Page 2151
- RoHS

- SW
- SR
- BL

Information

T-Handles GN 563.2 can be used as either operating handles or for clamping purposes, producing high clamping forces.

T-Handle screws are forged in a die and therefore have a structure with a higher stability and a smooth surface.

Original ELESA design, produced in metal in agreement with ELESA S.p.a.

see also...

- T-Handles GN 563 (Plastic) → Page 92

2.4

How to order	
1	Length l
2	d ₁ (d ₂)
3	Finish

GN 563.2-67-M8-SW