


elesa
Original design BT-AV-B

3 Type
E With threaded blind bore



1 2 d₁				d₂	d₃	h	k	t min.	Drive SL for slotted screwdriver
12				M 3 M 4 M 5	9,5	12	8	6	SL 6,5
16				M 3 M 4 M 5	11	13,5	8,5	6	SL 6,5
20				M 5 M 6 -	11,5	16	10	6	SL 10

Specification

Knob	
Plastic, polyamide (PA)	
• Reinforced	
• Operating temperature -30 °C to +130 °C	
• Black, matte finish	
Bushing	
Brass	MS
RoHS	

Knurled nuts GN 592 are used for quick, tool-free mounting or adjusting of fixtures and devices.
If higher tightening or loosening torques are required, the slot can be used to drive the nut with a screwdriver.

see also...	Page
GN 592 Knurled Screws (Threaded Stud Steel)	QVX
GN 530 Knurled Nuts (Phenolic Resin)	QVX
GN 590.5 Knurled Nuts (Bushing Stainless Steel)	QVX
GN 420 Knurled Nuts (Bushing Steel Zinc Plated)	QVX

Technical Information	
Plastic Characteristics	QVX

How to order		1	d ₁
		2	d ₂
		3	Type
		4	Material
GN 592- 20 - M5 - E - MS			