



d ₁	d ₂		Material				d ₃	d ₄	l ₁	l ₂	l ₃
	Plastic	KT	Steel	ST	KT	ST					
14	-	-	M 6	-	-	-	8	11	28	10	0,5
18	M 6	-	M 6	-	M 6	-	10	15	40	12	2,5
21	M 6	M 8	M 6	M 8	M 6	M 8	10	17	50	13	2,5
22	M 6	M 8	M 6	M 8	-	-	10	18	56	13	2,5
23	M 8	M 10	M 8	M 10	M 8	M 10	13	19	65	14	2,5
26	M 8	M 10	M 8	M 10	M 8	M 10	13	21	80	16	2,5
28	M 10	-	M 10	-	M 10	-	13	22	90	16	2,5
31	M 12	-	-	-	M 12	-	14	25	102	20	2,5

Specification

Handle

- Plastic, phenolic resin (PF) **KU**
 - Operating temperature up to 110 °C
 - Black, shiny finish
- Plastic, Polypropylen (PP) **KT**
 - Operating temperature up to 80 °C
 - Black, matte
 - Black, shiny finish (only size 14)
- Steel **ST**
 - Powder coated
 - Black, textured finish

Spindle

- Steel
- Zinc plated, blue passivated

RoHS

On request

With inch threads

Steel revolving handles GN 598 are mainly used on safety handwheels to increase imbalance and thus avoid free wheeling.

see also...

	Page
GN 598.1 Revolving Handles (Spindle Stainless Steel)	QVX
GN 539 Fixed Cylindrical Handles	QVX
GN 598.3 Retractable Handles (with hold in both positions)	QVX

Technical Information

Plastic Characteristics	QVX
-------------------------	-----

How to order

GN 598-KU-21-M8

1	Material
2	d ₁
3	d ₂