




elesa
Original design BTL.

<div>1</div> <div>d₁</div>	<div>2</div> <div>d₂</div>	<div>3</div> <div>Length l</div>	<div>d₃</div>	<div>h</div>	<div>k</div>	<div>t min.</div>
20	M 5	-	11	21	12	10
20	M 6	16	11	21	12	12
25	M 6	-	16	26	15	12
25	M 8	20	16	26	15	13
32	M 8	25	17	30	17	15

Specification

Knob Plastic, polyamide (PA) • Glass fiber reinforced • Operating temperature -30 °C to +130 °C • Black, matte finish	
Threaded bushing Brass	MS
Threaded stud Steel Zinc plated, blue passivated	ST
RoHS	

Knurled nuts and knurled screws GN 590.1 are used for quick, tool-free mounting or adjusting of fixtures and devices.

see also... [ganternorm.com](https://www.ganternorm.com)

- GN 530 Knurled Nuts (Phenolic Resin)
- GN 590.13 Knurled Nuts / Knurled Screws (with Extended Bushing, with Loss Protection)
- GN 590.5 Knurled Nuts (Threaded Bushing Steel / Stainless Steel)
- GN 591 Knurled Screws (Threaded Stud Steel / Stainless Steel)
- GN 420 Knurled Nuts (Threaded Bushing Steel / Stainless Steel)
- GN 421 Knurled Screws (Threaded Stud Steel / Stainless Steel)

Technical Information

Plastic Characteristics

How to order (Threaded bushing)	1 d ₁
<div>1 2 4</div> GN 590.1-20-M5-MS	2 d ₂
	4 Material

How to order (Threaded stud)	1 d ₁
<div>1 2 3 4</div> GN 590.1-25-M8-20-ST	2 d ₂
	3 Length l
	4 Material