

Type A




elesa

Original design I.281 / I.281+x-SST



4 Type

- A** With threaded bolt
- E** Without threaded bolt



Type E

2 d_1	3 d_2 6g Type A		3 d_3 ^{+0,3} / _{+0,1} Type E	d_4	d_5	l_1	l_2	l_3	l_4	l_5	A/F
18	M 6	-	8	15	12	40	13	0,3	39	35	4
21	M 8	-	10	17	14	50	15	0,5	49	43	5
23	M 8	M 10	12	19	16	65	17	0,5	64	56	6
26	M 10	-	13	21	17	80	18	0,5	79	70	6
28	M 10	-	14	22	19	90	18	0,5	89	79	8
31	M 12	-	16	25	20	102	20	1	100	89	8

Specification

Handle

- Plastic, phenolic resin (PF)
- Operating temperature -20 °C to +110 °C
- Black, shiny finish



KU

Spindle for type A

Stainless steel AISI 304

RoHS

The outstanding feature of revolving handles GN 598.2 is their highly robust design. Type E is suitable for use in connection with user-specific threaded bolts.

see also...

GN 598.1 Revolving Handles (Spindle Stainless Steel) Page QVX

Technical Information

Plastic Characteristics QVX

Stainless Steel Characteristics QVX

How to order

1 Material
2 d_1
3 d_2 (d_3)
4 Type

GN 598.2-KU-31-M12-A