




elesa
Original design BTL-RC / BTL-LP

- 5 Type**
- R** With retaining ring
 - P** With plastic ball chain

1 d ₁	2 d ₂	3 Length l	d ₃	h ₁	h ₂	k	r	t min.
20	M 5	-	11	21	2,5	12	20	10
20	M 6	16	11	21	2,5	12	20	12
25	M 6	-	16	26	3,5	15	21,5	12
25	M 8	20	16	26	3,5	15	21,5	13
32	M 8	25	17	30	3,5	17	21,5	15

Specification		4
Knob		
Plastic, polyamide (PA)		
• Glass fiber reinforced		
• Black, matte finish		
Threaded bushing		
Brass	M	
Threaded stud		
Steel	S	
Zinc plated, blue passivated		
Retaining ring / Ball chain		
Plastic, polyacetal (POM)		
Black		
Key ring on type P		
Stainless steel AISI 301		
Chemically blackened		

Operating temperature 0 °C to +60 °C

RoHS

Accessory	ganternorm.com
GN 111.3 Key Rings (Stainless Steel)	
GN 111 Ball Chains (Brass)	
GN 111.5 Ball Chains (Stainless Steel)	
GN 111.2 Retaining Cables (Stainless Steel)	
GN 111.8 Retaining Cables (Stainless Steel Quality Class 4)	
GN 111.4 Spiral Retaining Cables (Plastic)	

Knurled nuts and knurled screws GN 590.13 are used for quick, tool-free mounting or adjusting of fixtures and devices.

The affixed retaining ring allows knurled nuts and knurled screws GN 590.13 to be secured with a ball chain or retaining cable to prevent loss.

Type P is delivered with attached retaining ring and ball chain.

see also... ganternorm.com

GN 590.1 Knurled Nuts / Knurled Screws (with Extended Bushing)

GN 530 Knurled Nuts (Phenolic Resin)

GN 590.5 Knurled Nuts (Threaded Bushing Stainless Steel)

GN 420 Knurled Nuts (Threaded Bushing Steel / Stainless Steel)

Technical Information

Plastic Characteristics

Stainless Steel Characteristics

How to order (Threaded bushing)	
1 d ₁	
2 d ₂	
4 Material	
5 Type	

GN 590.13-20-M5-M-R

How to order (Threaded stud)	
1 d ₁	
2 d ₂	
3 Length l	
4 Material	
5 Type	

GN 590.13-25-M8-20-S-P