



**elesa**  
Original design ERM.SST-p



1		2		3													
$l_1$	$d_1$			$l_2$				$d_2$	$d_3$	$h_1$	$h_2$	$h_3$	$h_4$		Stroke		
44	M 4	-	-	12	16	20	25	32	-	-	10	14,5	24,5	3,5	30	3,5	
44	M 5	M 6	-	12	16	20	25	32	40	50	10	14,5	24,5	3,5	30	3,5	
63	M 6	M 8	-	16	20	25	32	40	50	63	13,5	18	31	3,5	38	4	
78	M 8	M 10	M 12	20	25	32	40	50	63	80	16	21,5	36	3,5	46	4	
95	M 10	M 12	-	20	25	32	40	50	63	80	19	25	43	5	56	4	

**Specification**

- Handle  
Zinc die casting
- Powder coated  
Black, RAL 9005, textured finish **● SW**  
Orange, RAL 2004, textured finish **● OS**  
Red, RAL 3000, textured finish **● RS**  
Silver, RAL 9006, textured finish **● SR**
- Threaded stud and retaining screw  
Stainless steel AISI 303
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**Information**

Adjustable hand levers GN 602.1 like all the products of the Ergostyle® family are renowned for their good style but also their ergonomic shape.

The gently arched handle with a reinforced end of the lever gives the operator a good grip.

Pulling the lever disengages the serration and allows it to be turned in either direction to reach the ideal new location. On releasing the handle the serrations re-engage automatically.

see also...

- *Product Family Ergostyle®* → Page 18
- *Adjustable Hand Levers GN 602 (Zinc Die Casting, Threaded Stud Steel)* → Page 457
- *Adjustable Hand Levers GN 604.1 (Handle Plastic, Threaded Stud Stainless Steel)* → Page 463

How to order

1	$l_1$
2	$d_1$
3	$l_2$
4	Color

**GN 602.1-44-M6-32-SB**

