




elesa
Original design BT-AV-p

1					2		3	
d ₁	d ₂	Length l			d ₃	h	k	Drive SL for slotted screwdriver
12	M 3	6	10	-	9,5	12	8	SL 6,5
12	M 4	6	10	-	9,5	12	8	SL 6,5
12	M 5	10	16	-	9,5	12	8	SL 6,5
16	M 3	6	10	-	11	13,5	8,5	SL 6,5
16	M 4	6	10	16	11	13,5	8,5	SL 6,5
16	M 5	10	16	-	11	13,5	8,5	SL 6,5
20	M 5	10	16	20	11	16	10	SL 10
20	M 6	10	16	25	11	16	10	SL 10

Specification

Knob	
Plastic, polyamide (PA)	
• Reinforced	
• Operating temperature -30 °C to +130 °C	
• Black, matte finish	
Threaded stud	
Steel	ST
Zinc plated, blue passivated	
RoHS	

Knurled screws GN 592 are used for quick, tool-free mounting or adjusting of fixtures and devices.
If higher tightening or loosening torques are required, the slot can be used to drive the screw with a screwdriver.

see also...	Page
GN 592 Knurled Nuts (Bushing Brass)	QVX
GN 529 Knurled Screws (Phenolic Resin)	QVX
GN 591.5 Knurled Screws (Threaded Stud Stainless Steel)	QVX
GN 421 Knurled Screws (Threaded Stud Steel Zinc Plated)	QVX

Technical Information	
Plastic Characteristics	QVX

How to order	1 d ₁
	2 d ₂
	3 Length l
	4 Material
GN 592-12-M4-10-ST	