



elesa
Original design ERM.p



1.1

1.2

1.3

1.4

1		2		3													
l_1	d_1			l_2				d_2	d_3	h_1	h_2	h_3	h_4		Stroke		
44	M 4	-		12	16	20	25	32	-	-	-	10	14,5	24,5	3,5	30	3,5
44	M 5	M 6		12	16	20	25	32	40	50	-	10	14,5	24,5	3,5	30	3,5
63	M 6	M 8		12	16	20	25	32	40	50	63	13,5	18	31	3,5	38	4
63	M 10	-		20	25	32	40	50	63	80	-	13,5	18	31	3,5	38	4
78	M 8	M 10		16	20	25	32	40	50	63	80	16	21,5	36	3,5	46	4
78	M 12	-		20	25	32	40	50	63	80	-	16	21,5	36	3,5	46	4
95	M 10	M 12		16	20	25	32	40	50	63	80	19	25	43	5	56	4
95	M 16	-		25	32	40	50	63	80	-	-	19	25	43	5	56	4

2.1

Specification

- Handle
Zinc die casting
- Powder coated
Black, RAL 9005, textured finish **● SW**
Orange, RAL 2004, textured finish **● OS**
Red, RAL 3000, textured finish **● RS**
Silver, RAL 9006, textured finish **● SR**
- Threaded stud and retaining screw
Steel
- Property class 5.8
- Blackened
- Strength Values of Screws → Page 2152
- RoHS

4

Information

Adjustable hand levers GN 602, like all the products of the Ergostyle® family, are renowned for their good style but also their ergonomic shape.

The gently arched handle with a reinforced end of the lever gives the operator a good grip.

Pulling the lever disengages the serration and allows it to be turned in either direction to reach the ideal new location. On releasing the handle the serrations re-engage automatically.

see also...

- Product Family Ergostyle® → Page 18
- Adjustable Hand Levers GN 602.1
(Zinc Die Casting, Threaded Stud Stainless Steel) → Page 459
- Adjustable Hand Levers GN 604 (Plastic, Threaded Stud Steel)
→ Page 461

2.2

2.3

2.4

How to order		1	l_1
		2	d_1
GN 602-95-M12-40-OS		3	l_2
		4	Color

