



1.1
1.2
1.3
1.4

1	2	3							
l_1	d_1	l_2		d_2	d_3	h_1	h_2	h_3	h_4 Stroke
44	M 6	16	25	12	15,5	29	9	36	3,5
63	M 8	20	30	15	19	37	12	48	4

2.1

Specification

- Handle
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 130 °C
- Black-gray, similar RAL 7021, matte ● **SG**
- Threaded stud and retaining screw
Steel, blackened
- *Plastic Characteristics* → Page 2158
- **RoHS**



Information

The design and handling of the adjustable hand lever GN 604.2 satisfy the high standards of the Ergostyle® product family.

Safety hand levers GN 604.2 are used where the inadvertent loosening or readjustment can result in accidents.

If not operated, the lever is not linked to the threaded insert, i.e. the hand lever turns freely.

As soon as the lever hub is pushed down, both serrations will engage, allowing the fixture to be released or clamped.

After „releasing“, the connection disengages through spring tension.

see also...

- *Product Family Ergostyle®* → Page 18
- *Safety Tension Levers GN 312* → Page 497
- *Safety Star Knobs GN 5337.3* → Page 571

2.2

2.3

2.4

How to order	1	l_1
	2	d_1
	3	l_2
	4	Color
GN 604.2-44-M6-25-SG		

