Adjustable Hand Levers

Plastic, Threaded Bushing Stainless Steel, with Release Button, with Loss Protection







elesa

Original design ERX-SST-RC / -LP

STAIN LESS

4 Type

R With retaining ring
P With plastic ball chain

1 l_1	2 d_1	d_2	d_3	h_1	h_2	h_3	h_4 Stroke	r	t min.
44	M 6	12	16	29,5	6	32,5	3,5	21	10
63	M 8	15	19	37,5	8	43	4	22,5	13
78	M 10	19	23	47	12	54	4	24	18

Specification

3

Handle
Plastic, polyamide (PA)
- Glass fiber reinforced
- Black-gray, matte finish similar to RAL 7021

Release button
Plastic, polyamide (PA)
Black-gray, RAL 7021, shiny finish

Insert
Plastic, polyamide (PA)
- Glass fiber reinforced
- Black
- Threaded bushing
  Stainless steel AISI 303 **N**

Retaining ring / Ball chain
Plastic, polyacetal (POM), black

Key ring on type P
Stainless steel AISI 301, chemically blackened

Operating temperature 0 °C to +60 °C

RoHS

Accessory ganternorm.com

GN 111.3 Key Rings (Stainless Steel)
GN 111 | GN 111.5 Ball Chains (Brass / Stainless Steel)
GN 111.2 Retaining Cables (Stainless Steel)
GN 111.8 Retaining Cables (Stainless Steel Quality Class 4)

Adjustable hand levers GN 603.13 feature the same premium design and convenient handling as all products of the Ergostyle® family.
Like all adjustable hand levers, they are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the handle via serrations and can easily be disengaged.
The release button offers easy disengagement. Its use is limited to applications where dismantling of the lever for installation is not required.
The affixed retaining ring allows adjustable hand levers GN 603.13 to be secured with a ball chain or retaining cable to prevent loss. Type P is delivered with attached retaining ring and ball chain.

see also... ganternorm.com

GN 603 Adjustable Hand Levers (with Release Button, Threaded Bushing Brass)
GN 603.1 Adjustable Hand Levers (with Release Button, Threaded Bushing Stainless Steel)
GN 603.4 Adjustable Hand Levers (with Release Button, Plastic, Chrome-Plated)
GN 600 Flat Adjustable Hand Levers (mit Release button)

Technical Information

Product Family Ergostyle®
Plastic Characteristics
Stainless Steel Characteristics

How to order

1 2 3 4
GN 603.13-78-M10-N-R

1	l_1
2	d_1
3	Material
4	Type