



3 Type

A Full ball

d ₁	l ₁				d ₂	l ₂ ≈	A/F	Static load in N
	Nominal length							
M 6 x 0,75	10	16	20	25	4	1,3	3	9000
M 8 x 1	12	20	25	30	5,5	1,8	4	15000
M 10 x 1	16	20	25	35	7	2,3	5	24000

Specification

Steel

- Screw
 - Tempered
 - Blackened

- Ball
 - Hardened
 - Plain

RoHS

Ball point screws GN 605 with full ball (type A) are used in applications where a ball point contact is required.

The fine thread increases the self-locking action and allows for finer adjustment.

see also...

	Page
GN 605 Ball Point Screws (Steel, with Standard Thread)	QVX
GN 605 Ball Point Screws (Stainless Steel, with Standard Thread)	QVX
GN 606 Ball Point Screws (with Cylindrical Knob)	QVX
GN 913.2 Grub Screws (with Hardened Pad)	QVX

How to order

GN 605-M6x0,75-10-A

1 d₁

2 l₁

3 Type