



<div>1</div> <div>2</div> <div><math>l_1</math></div>	$d_1$	$d_2$	$d_3$	$h_1$	$h_2$	$h_3$	$h_4$ Stroke	$t$ min.
44	M 6	12	15,5	29,5	6	32,5	3,5	10
63	M 8	15	19	37,5	8	43	4	13
78	M 10	19	23	47	12	54	4	17
95	M 12	21,5	26,5	54,5	13	64,5	4,5	20

Specification

- Handle  
Plastic  
Technopolymer (Polyamide PA)
  - Glass fiber reinforced
  - Temperature resistant up to 80 °C
  - Chrome plated, shiny
- Color of the releasing button  
Black, shiny
- Threaded bushing  
Brass
- *Plastic Characteristics* → Page 2158
- RoHS

On request

- With threaded stud

Information

Adjustable hand levers GN 603.4, like all the products of the Ergostyle® range, are renowned for their good style but also their ergonomic shape.

The gently arched handle with a reinforced end of the lever gives the operator a good grip when resting the thumb on the press button to disengage the serration for re-adjusting the lever position in either direction.

With the lever disengaged the thread insert can also be screwed in with the help of the serration.

Its use is, however, limited to applications where dismantling of the lever for installation is not required.

- see also...
- *Product Family Ergostyle®* → Page 18
  - *Adjustable Hand Levers GN 603*  
(with Realeasing Button, Bushing Brass) → Page 468

How to order	1	$l_1$
<div>GN 603.4-95-M12</div>	2	$d_1$