



1		2								
l_1	d_1			d_2	d_3	h_1	h_2	h_3	h_4	t min.
63	M 6	M 8	-	13,5	19	31	3,5	38,5	4	10
78	M 8	M 10	M 12	16	23	36	3,5	46,5	4	14

Specification

- Handle
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 130 °C
- Black-gray, RAL 7021, matte **● SGA**
- White, RAL 9016, matte **○ WSA**
- Annular gear ring
Zinc die casting
- Threaded bushing and retaining screw
Stainless steel AISI 303
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

Adjustable hand levers GN 604.1 are manufactured from an antimicrobial plastic.

Adding a silver-based substance has created a natural active agent that helps to prevent the growth of bacteria. Even after repeated cleaning with soap or solvent, the antimicrobial effect of this additive will not diminish. Sterilising at temperatures below 130 °C will also have no effect on the antimicrobial property.

With these properties, the handles are the perfect choice for use in medical engineering, in the food and the pharmaceutical industry, and in general wherever hygiene is of great importance.

see also...

- *Product Family Sanline* → Page 2154
- *Product Family Ergostyle®* → Page 18
- *Adjustable Hand Levers GN 604 (Plastic, Bushing Steel)* → Page 460
- *Adjustable Hand Levers GN 602.1 (Zinc Die Casting, Bushing Stainless Steel)* → Page 458
- *Adjustable Hand Levers GN 604.1 (Plastic, Bushing Stainless Steel)* → Page 462

How to order

1	l_1
2	d_1
3	Finish

GN 604.1-78-M8-SGA