



3 Type

- N** Neutral
- M** With arrow
- S** With scale 0...9
20 graduations

1

2

d ₁ 17	d ₂ H8 Bore	d ₃	d ₄	d ₅	d ₆	l ₁	l ₂	l ₃	t ₁	t ₂
27	B 6	22	25	20,5	M 4	30	12	18	24	12
32	B 8	25	30	25	M 4	38	13	23	30	13
35	B 10	28	33	26,5	M 5	45	15	27	37	15
40	B 12	33	38	31	M 5	52	16,5	32	44	16

Specification

- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 130 °C
 - Black, shiny finish
- Arrow (Type M) and scale (Type S)
White, engraved with laser precision
- Grub screw DIN 916 with internal hexagon and serrated point
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- RoHS

On request

- Special graduations see „How to Order Graduations“

→ Page 326

Information

Besides the standard scale (Type S) the control knobs GN 626 can be supplied with any type of graduation.

Regarding design, numbering run, numbering position and numbering sequence of the scale please see the layout for scale knobs on the order sheet „How to Order Graduations“ → Page 326.

see also...

- Control Knobs GN 526 (Plastic) → Page 332
- Control Knobs GN 726 / GN 726.1 (Aluminum) → Page 335 / 336
- Clamping Elements GN 826 (for Adjustable Spindles) → Page 346

How to order

GN 626-40-B12-N

1	d ₁
2	d ₂
3	Type