



Type **A**



Type **B**



elesa
Original design EWP.

iF product design award

2 Type

A Mounting with hex head screw
B Mounting with countersunk screw

1

l_1	b_1	b_2	d	h_1	h_2	h_3	h_4	l_2 ±0,5	l_3	t
114	35	19	6,5	33	7	11	6	93,5	74	5

Specification

3

Handle
Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +110 °C
- Black-gray, matte finish, similar to RAL 7021

Cover caps
Plastic, Polyamide (PA)
- Black-gray, RAL 7021, shiny finish **DSG**
- Orange, RAL 2004, shiny finish **DOR**
- Gray, RAL 7035, shiny finish **DGR**
- Yellow, RAL 1021, shiny finish **DGB**
- Blue, RAL 5024, shiny finish **DBL**
- Red, RAL 3000, shiny finish **DRT**
- Green, RAL 6017, shiny finish **DGN**

RoHS

The design of the cabinet U-handles GN 630.1 matches the product family of Ergostyle®.
A typical application is on double swing doors on machine shrouds or fixtures.
The cover caps shroud the two mounting screws of the cabinet U-handle.
The cover caps are supplied loose.

see also...	Page
GN 630 Ledge Handles (Polyamide)	QVX
GN 565.2 Inclined Cabinet U-handles (Aluminum, Mounting from the Back or the Operator's Side)	QVX
GN 425.1 Cabinet U-Handles (Steel / Aluminum / Stainless Steel, Angled)	QVX

Technical Information

Product Family Ergostyle®	QVX
Strength Properties	QVX
Overview of Standard Parts for Profile Systems	QVX
Plastic Characteristics	QVX

How to order
1 2 3
GN 630.1-114-A-DOR

1	l_1
2	Type
3	Color of the cover cap